








APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	12/20/12	
A		REVISED SPEC.	2/10/14	AY/TW



SPECIFICATIONS:
Material: Insulator: Hi-temp thermoplastic, rated UL 94V-0
Insulator color: Black
Contacts: Copper Alloy
Shell: Stainless Steel, Tin plated
Plating: Gold flash over Nickel underplate overall
Electrical: Current Rating: 1.0A AC/DC.
Rated Voltage: 30 V Max.
Contact resistance: 60 mohms max.
Insulation resistance: 100 Mohms min.
Dielectric withstanding voltage: 100 VAC for 1 minute
Temperature Rating: Operating temperature: -25°C to +85°C
Environmental: Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

MICRO USB B TYPE, FEMALE, VERTICAL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				Holes			
.X	± .10	ØX	± .10	.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010				
APPROVALS				DATE			
DRAWN	AY		12/20/12				
CHECKED	YC		12/20/12				
APPROVED							
				TITLE			
				MICRO USB B TYPE, FEMALE, VERTICAL			
				SIZE PART NO.			
				X MCR-B-S-VT-01			
				REV. A			
				SCALE: NTS SHEET 1 OF 1			