

6

5

4

3

2


1

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/23/06	


APPROVED: _____

DATE: _____ TITLE: _____

D



C



B

SPECIFICATIONS:

Material:

Insulator: PBT, glass filled, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Shield: Copper Alloy, Tin plated

Plating:

Gold over Nickel underplate on contact area, Tin over

Copper underplate on tails

Electrical:

Operating voltage: 100 VAC/12 VDC max.

Current rating: 1 Amp max./2 Amps max.

Contact resistance: 20 mohms max. initial

Insulation resistance: 500 Mohms min.

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +70°C

Environmental:

Lead free, RoHS compliant.

Recommended soldering temp: 235 for 5 sec.

A

A

B

C

D

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

MINI DIN JACK, STACKED 4 POSITION
RIGHT ANGLE, FULLY SHIELDED

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLDS				ADAM TECH			
.X ± .10 ØX ± .10 .XX ± .020 ØXX ± .015 .XXX ± .015 ØXXX ± .010				909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
APPROVALS		DATE		TITLE			
DRAWN SS		1/23/06		MINI DIN JACK, STACKED 4 POSITION RIGHT ANGLE, FULLY SHIELDED			
CHECKED				SIZE PART NO.			
APPROVED				X MDJD-004-FS			
REF:		SCALE: NTS		SHEET 1 OF 1		REV.	