


Rev	AWO #	Description	Date	Appr
-		RELEASED	10/30/09	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material: Insulator: PBT, glass reinforced, rated UL 94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Plating: Gold flash over Nickel underplate overall
Electrical: Current rating: 2 Amp max
Contact resistance: 30 mohms max
Insulation resistance: 1,000 Mohms min
Dielectric withstanding voltage: 650 VAC for 1 minute
Temperature Rating: Operating temperature: -55°C to $+105^{\circ}\text{C}$
Environmental: Lead free, RoHS compliant

Positions: 2 thru 11
A = $.079$ [2.00] x No. of Positions
B = $.079$ [2.00] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		TITLE	
INCHES		.079 [2.00] GANGED MINI SHUNT, OPEN TOP	
.X ± .10		.169 [4.30] HEIGHT, GOLD PLATED	
.XX ± .020			
.XXX ± .015			
APPROVALS		DATE	
DRAWN		10/30/09	
CHECKED			
APPROVED			
SIZE		PART NO.	
X		MS2BG-XX-G	
REF: S0007T		SCALE: NTS	
		SHEET 1 OF 1	

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710