

6

5

4

3


2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/6/05	
A		CHANGED AMP TO 3A, WAS 1A	5/3/06	
B		REDRAWN	9/20/11	
C		UPDATE SPEC.	9/11/19	AY/BC



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy

Plating:

G = Gold flash over Nickel underplate overall

T = Tin over Copper underplate overall

Electrical:

Current rating: 3 Amp max

Contact resistance: 30 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 650 VAC for 1 minute

Temperature Rating:

Operating temperature: -55°C to +105°C

Environmental:

Lead free, RoHS compliant.

RoHS
COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 ØX ± .10
.XX ± .020 ØXX ± .015
.XXX ± .015 ØXXX ± .010

APPROVALS DATE

DRAWN SS 4/6/05

CHECKED

APPROVED

ADAM
TECH
INTERCONNECTS 909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

.100 [2.54] MINI SHUNT, HANDLE TOP

.531 [13.50] HEIGHT

SIZE	PART NO.	REV.
X	MSBH-X	C
REF: S00076T	SCALE: NTS	SHEET 1 OF 1

6

5

4

3

2

1