






APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/8/05	
A		REVISED SPEC.	11/18/10	
B		REDRAWN	2/20/13	



SPECIFICATIONS:

Material: Contact: Brass, Tin plated
Electrical: Operating voltage: 250 V AC/DC
Current rating: 3 A AC/DC
Contact resistance: 20 mohms max
Dielectric withstanding voltage: 1,000 VAC for 1 minute
Thickness: 0.2mm
Wire Range: AWG#22~#28
Insulation O.D: 1.5mm
Temperature Rating: Operating temperature: -25°C to +85°C
Packaging: B = loose cut
R = tape and reel
Environmental: Lead free, RoHS compliant



ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

CRIMP CONTACT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				TITLE			
INCHES	HOLES	DATE		SIZE	PART NO.	REV.	
.X ± .10	ØX ± .10			X	MTA-C-X	B	
.XX ± .020	ØXX ± .015			REF:	S00016T	SCALE: NTS	SHEET 1 OF 1
.XXX ± .015	ØXXX ± .010						
DRAWN	SS	4/8/05					
CHECKED							
APPROVED							