





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/4/04	
A		REDRAWN	11/04/11	
B		UPDATE SPEC.	8/1/18	AY/RC1
C		UPDATE SPEC.	12/20/18	AY/DH



RECOMMENDED PCB LAYOUT



SECTION A-A

SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Insulator color: Gray

Contacts: Phosphor Bronze

Contacts Plating:

Round contact

Gold over Nickel underplate overall

Flat contact

Gold over Nickel underplate on contact area

Tin over Nickel underplate on solder tails

Electrical:

Voltage rating: 150 VAC rms

Current rating: 1.5 Amp

Contact resistance: 35 mohms max

Insulation resistance: 1,000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +85°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	SS	10/4/04
CHECKED		
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE			
MODULAR TELEPHONE JACK, 6P6C RIGHT ANGLE, PCB, COLOR GRAY			
SIZE X	PART NO. MTJ-662X2	REV. C	
REF: S00005C	SCALE: NTS	SHEET 1 OF 1	