



APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/4/04	
A		UPDATE DRAWING	11/30/17	AY/SL



SPECIFICATIONS:

Material:
 Insulator: PBT, Glass Fiber, rated UL 94V-0
 Insulator color: Black
 Contacts: Phosphor Bronze
 Plating:
 Gold over Nickel underplate overall
 Electrical:
 Voltage Rating: 150 VAC max
 Current rating: 1.5 Amps max
 Contact Resistance: 20 mohms max.
 Insulation resistance: 500 Mohms min @500 VDC
 Dielectric withstanding voltage: 1000 Vrms for 1 minut
 Temperature Rating:
 Operating temperature: -40°C to +85°C
 Environmental:
 Lead free, RoHS Compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		ADAM TECH		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
INCHES		HOLES		INTERCONNECTS	
.X	± .10	Ø.X	± .10	TITLE	
.XX	± .020	Ø.XX	± .015	MODULAR TELEPHONE JACK, 6P6C	
.XXX	± .015	Ø.XXX	± .010	RIGHT ANGLE, PCB	
APPROVALS		DATE		SIZE	
DRAWN	SS	10/4/04		PART NO.	
CHECKED				MTJ-667X1	
APPROVED				REV.	
				A	
REF:		S00065T		SCALE: NTS	
				SHEET 1 OF 1	