





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	04/28/05	
A		REDRAWN	6/3/15	AY/AC
B		UPDATE DRAWING	10/2/18	AY/OC



SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Shield: Brass, Nickel plated

Contacts Plating:

Round contact

Gold over Nickel underplate overall

Flat contact

Gold over Nickel underplate on contact area,

Tin over Nickel underplate on solder tails

Electrical:

Voltage rating: 150 VAC rms

Current rating: 1.5 Amps

Contact resistance: 20 mohms max

Insulation resistance: 1000 Mohms min @ 500 VDC

Dielectric withstanding voltage:

Contact to Contact: 1,000 VDC or AC Peak for 1 minute

Contact to Screen and Test panel: 1,500 VDC or AC Peak for 1 minute

Temperature Rating:

Operating temperature: -40°C to +85°C

Environmental:

Lead free, RoHS compliant.

RECOMMENDED PCB LAYOUT



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS DATE

DRAWN SLS 04/28/05

CHECKED

APPROVED

ADAM 909 Rahway Avenue,
TECH Union, NJ 07083
INTERCONNECTS Phone: 908-687-5000
Fax: 908-687-5710

TITLE
MODULAR GANGED JACK, 4 PORT, 8P8C,
RIGHT ANGLE SHIELDED

SIZE PART NO. REV.
X MTJG-4-88GX1-FSB B

REF: S00005C SCALE: NTS SHEET 1 OF 1