





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	03/11/13	
A		UPDATE SPEC.	5/22/18	AY/RC



SPECIFICATIONS:

Material:

Insulator: ABS, rated UL 94V-0

Insulator color: Gray

Contacts: Phosphor Bronze

Wires: 26AWG, Stranded, UL1061

Plating:

Gold over Nickel underplate on mating area

Electrical:

Voltage rating: 125 VAC RMS

Current rating: 1.5 Amp

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1,000 VAC or 1500 VDC RMS for 1 minute

Temperature Rating:

Operating temperature: 0°C to +70°C

Environmental:

Lead free, RoHS compliant



X	PLATING
0	15 µin Gold
1	30 µin Gold
2	50 µin Gold

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES		ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
.X ± .10 ØX ±.10 .XX ± .020 Ø.XX ±.015 .XXX ± .015 Ø.XXX ±.010					
APPROVALS		DATE		TITLE WIRE LEADED TELEPHONE JACK., 616W, 4P4C, 26AWG, STRIPPED & TINNED	
DRAWN	TW	03/11/13			
CHECKED	EC	03/11/13			
APPROVED					
		SIZE X	PART NO. MTJP-616W-X-A1-2	REV. A	
		REF: S00005C	SCALE: NTS	SHEET 1 OF 1	