





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/4/04	
A		REDRAWN	10/23/12	



SECTION A-A

"X"	PLATING
X	Gold flash
U	15 µin Gold
W	30 µin Gold
G	50 µin Gold

SPECIFICATIONS:

Material:
Insulator: Polycarbonate, rated UL 94V-0
Insulator color: Clear
Contacts: Phosphor Bronze
Plating:
Gold over Nickel underplate on contact area
Electrical:
Insulation resistance: 1,000 Mohms min
Dielectric withstanding voltage: 1,000 VAC for 1 minute
Environmental:
Lead free, RoHS compliant



ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

MODULAR TELEPHONE PLUG, 4P4C
STANDARD OVAL WIRE TYPE

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
INCHES		HOLES		TITLE			
.X	± .10	ØX	±.10	MODULAR TELEPHONE PLUG, 4P4C STANDARD OVAL WIRE TYPE			
.XX	± .020	ØXX	±.015				
.XXX	± .015	ØXXX	±.010				
APPROVALS				DATE			
DRAWN	SS	10/4/04		SIZE			
CHECKED				PART NO.			
APPROVED				MTP-44-X			
REF: S00005C				SCALE: NTS		REV. A	
SHEET 1 OF 1							