

6

5

4

3

2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev

AWO #

Description

Date

Appr

-

RELEASED

9/25/20

D

D

C




C

B


B

A

A



SECTION A-A



"X"	PLATING
X	Gold flash
U	15 µin Gold
W	30 µin Gold
G	50 µin Gold

SPECIFICATIONS:

Material:

Insulator: PA6, rated UL 94V-0

Insulator color: Clear White

Contacts: Copper Alloy

Plating:

Gold over Nickel underplate on contact area

Electrical:

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,000 VAC For 1 Minute

Environmental:

Lead free, RoHS compliant

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED

MM	ANGLE
0~15 ± 0.15	± 1°
15~30 ± 0.20	
30~ ± 0.25	

APPROVALS

DATE

DRAWN

LH

9/25/20

CHECKED

AY1

9/25/20

APPROVED

ADAM
TECH909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

MODULAR TELEPHONE PLUG, 8P8C, CAT5

SIZE
X

PART NO.

MTPR-88-X-C

REV.
-

REF: S00005C

SCALE: NTS

SHEET 1 OF 1

6

5

4

3

2

1