






APPROVED: _____

DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	10/20/16	



RECOMMENDED PCB LAYOUT



SECTION A-A



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Shell: Phosphor Bronze, Gold plated

Plating:

10u" Gold over Nickel underplate on contact area

Electrical:

Voltage rating: 5 VAC

Current rating: 0.5 A

Contact resistance: 50 mohms max.

Insulation resistance: 100 Mohms min. @ 500 VDC

Withstanding voltage: 100 VAC for 1 minute

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS		DATE
DRAWN	HR	10/20/16
CHECKED	CH	10/20/16
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE
**MINI USB, 8P, FEMALE, SINGLE PORT,
RIGHT ANGLE, TRUE SMT TYPE**

SIZE	PART NO.	REV.
X	MUSB-8P-S-RA-TSMT-01-10	-
REF: S00126T	SCALE: NTS	SHEET 1 OF 1