

6

5

4

3






2

1

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/13/12	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Shell: Brass, Nickel Plated

Plating:

Gold Flash over Nickel underplate on contact area,

Tin over Copper underplate on PCB tails

Electrical:

Current Rating: 1.0 A AC/DC

Voltage Rating: 30 V AC/DC

Contact resistance: 50 Mohms max

Insulation resistance: 100 Mohms min

Dielectric withstanding voltage: 100 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +80°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MM
TOLERANCES: EXCEPT AS NOTED
.XX ± 0.25
.XXX ± 0.20

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

MINI USB, TYPE B, 5PIN, VERTICAL, TRUE SMT

APPROVALS		DATE	TITLE	
DRAWN	AY	7/13/12	SIZE	PART NO.
CHECKED	AH	7/13/12	X	MUSB-B5-S-VT-TSMT-1
APPROVED			REF:	S00126T
			SCALE:	NTS
			SHEET	1 OF 1