


APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/29/16	
A		UPDATE DRAWING	2/18/16	AY/LW



SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Shell: SPCC, Nickel plated

Plating:

Gold over Nickel underplate on contact area,

Tin over Copper underplate on solder tails

Electrical:

Current rating: 1 A max

Contact resistance: 30 Mohms max

Insulation resistance: 1,000 Mohms min @ 500VDC

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -55°C to +105°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	HR	1/29/16
CHECKED	LW	1/29/16
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE
MINI USB, TYPE B, 5PIN, MALE PLUG,
SINGLE PORT, SOLDER TYPE

SIZE	PART NO.	REV.
X	MUSB-B5P-S-S-CS1	A
REF: S00217T	SCALE: NTS	SHEET 1 OF 1