


APPROVED: _____
DATE: _____ TITLE: _____

CUSTOM CABLE ASSEMBLIES ARE
NON-CANCELLABLE/NON-RETURNABLE

Rev	AWO #	Description	Date	Appr
-		RELEASED	2/27/09	
A		UPDATED CABLE DRAWING AND MARKINGS	11/6/17	
B		UPDATED DRAWING	3/11/21	LH/KC



SPECIFICATIONS:

Electrical:

Current rating: 10 Amps

Voltage rating: 125V AC

Connectors:

P1 = Nema 5-15P, color black. ANSI/NEMA WD 6-2002

Adam Tech UL File # E256360

P2 = IEC C13 Female, color black, Adam Tech

UL File # E256360

Cable:

18/3 SVT, 60°C, N/A wire color (White, Black, Green),
jacket color black, UL & CSA. Adam Tech

UL File # E303525

Electrical Test:

All assemblies must be 100% tested for shorts, open continuity and
physical appearance.

Environmental:

Lead free, RoHS compliant.



NOTES:

1. UL HOLOGRAM LABELS MUST BE ON OUTSIDE OF EACH CARTON.
2. CORDS PACKAGED 100 PCS / CARTON

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED		ADAM TECH		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
INCHES		HOLES		TITLE	
.X ± .10	Ø.X ± .10	DRAWN		SS	
.XX ± .020	Ø.XX ± .015	CHECKED		DATE	
.XXX ± .015	Ø.XXX ± .010	APPROVED		1/5/05	
SIZE		PART NO.		REV.	
X		PC-0102076AC03		A	
REF:		SCALE: NTS		SHEET 1 OF 1	