

6

5

4

3



2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/19/18	



MATING ADAM PART: CA-ST6-PH2-254105-M

SPECIFICATIONS:

Electrical:

Rated Current & Voltage: 12VDC, 2A

Contact resistance: 50 mohms max

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS TOLERANCES: EXCEPT AS NOTED			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
MM		ANGLE			
0~6 ± 0.05 6~30 ± 0.10 30~150 ± 0.15	± 1°				
APPROVALS		DATE			
DRAWN	HR	9/19/18	TITLE POGO PIN PCB CONN, 2.54MM PITCH FEMALE, 2X3P, STRAIGHT, W/ PCB		
CHECKED	CK	9/19/18			
APPROVED					
REF: S00170C			SCALE: NTS		SHEET 1 OF 1

6

5

4

3

2

1