



APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/7/22	
A		UPDATE SPEC.	9/8/23	LH/RC



SPECIFICATIONS:

Material:

Insulator: PA66, rated UL 94V-0

Insulator Color: See Chart

Contacts: Copper Alloy, Tin Plated

Plating:

Electrical:

Voltage rating: 300 VAC max

Current rating: 15 Amp

Dielectric withstanding voltage: 1600 VAC for 1 minute

Mechanical:

Recommended Wire Size:

Solid: 24-16AWG (0.2-1.5mm²)

Stranded: 24-16AWG (0.2-1.5mm²)

Stripping Length: .315"-.394" (8-10mm)

Temperature Rating:


Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.



RECOMMENDED RAIL SIZE 35.0mm X 7.5mm



REB-B 2 A -XX	Color
CSA (Cross Sectional Area) Solid/Stranded	OR=Orange
24-16 Awg (0.2-1.5mm ²)	BU=Blue
	GY=Gray
	YG=Yellow/Green

ADAM-P/N	Color
REB-B2A-OR	ORANGE
REB-B2A-BU	BLUE
REB-B2A-GY	GRAY
REB-B2A-YG	YELLOW/GREEN

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES
.X	± .10	ØX ± .10
.XX	± .020	ØXX ± .015
.XXX	± .015	ØXXX ± .010

DRAWN	JJ	10/7/22
CHECKED	RC	10/7/22
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

**ADAM
TECH**

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE		REV.	
DIN RAIL TERMINAL BLOCKS, GUV 2 HOLE, 24-16 AWG		A	
SIZE	PART NO.		
X	REB-B2A-XX		
REF:	S00067C	SCALE:	NTS
		SHEET	1 OF 1