




APPROVED: _____

DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	10/7/22	
A		UPDATE SPEC.	9/8/23	LH/RC



SPECIFICATIONS:

Material:
 Insulator: PA66, rated UL 94V-0
 Insulator color: See chart
 Contacts: Copper Alloy, Tin Plated
 Plating:
 Electrical:
 Voltage rating: 600V
 Current rating: 50A
 Dielectric withstanding voltage: 2,200 VAC for 1 minute
Mechanical:
 Recommended Wire Size:
 Solid: 24-8AWG (0.2-10.0mm²)
 Stranded: 24-10AWG (0.2-6.0mm²)
 Stripping Length: .472" (12mm)
 Temperature Rating:
 Operating temperature: -40°C to +105°C
Environmental:
 Lead free, RoHS compliant.

RECOMMENDED RAIL SIZE
 35.0mm X 7.5mm



ADAM-P/N	Color
REB-A2D-BU	BLUE
REB-A2D-GY	GRAY
REB-A2D-YG	YELLOW/GREEN

CSA (Cross Sectional Area)	Color
Solid/Stranded	OR=Orange
Solid: 24-8 Awg (0.2-10.0mm ²)	BU=Blue
Stranded: 24-10 Awg (0.2-6.0mm ²)	GY=Gray
	YG=Yellow/Green

ADAM-P/N	Color
REB-A2D-BU	BLUE
REB-A2D-GY	GRAY
REB-A2D-YG	YELLOW/GREEN

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	∅X	±.10
.XX	± .020	∅XX	±.015
.XXX	± .015	∅XXX	±.010

DRAWN	WX	10/7/22
CHECKED	RC	10/7/22
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM TECH 909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE DIN RAIL TERMINAL BLOCKS, GUS, 2 HOLE, 24-8 AWG		
SIZE X	PART NO. REB-A2D-XX	REV. A
REF: S00067C	SCALE: NTS	SHEET 1 OF 1

