





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Aprr
-		RELEASED	4/1/22	
A		UPDATE DRAWING	9/8/23	LH/RC



RECOMMENDED RAIL SIZE
35.0mm X 7.5mm



CSA (Cross Sectional Area)	Solid/Stranded
Solid:	24-6 Awg (0.2-16.0mm ²)
Stranded:	24-8 Awg (0.2-10.0mm ²)

REB-A 2 E -XX	Color
OR	Orange
BU	Blue
GY	Gray
YG	Yellow/Green

ADAM-P/N	Color
REB-A2E-BU	BLUE
REB-A2E-GY	GRAY
REB-A2E-YG	YELLOW/GREEN

SPECIFICATIONS:

Material:
 Insulator: PA66, rated UL 94V-0
 Insulator color: See chart
 Contacts: Copper Alloy, Tin Plated
 Electrical:
 Voltage rating: 600V
 Current rating: 65A
 Dielectric withstanding voltage: 2,200 VAC for 1 minute
 Mechanical:
 Recommended Wire Size:
 Solid: 24-6AWG (0.2-16.0mm²)
 Stranded: 24-8AWG (0.2-10.0mm²)
 Stripping Length: .709" (18mm)
 Temperature Rating:
 Operating temperature: -40°C to +105°C
 Environmental:
 Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED		
INCHES		HOLES
.X ± .10		∅X ± .10
.XX ± .020		∅XX ± .015
.XXX ± .015		∅XXX ± .010
DRAWN	WX	10/7/22
CHECKED	RC	10/7/22
APPROVED		
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH		

ADAM TECH 909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE		REV.
DIN RAIL TERMINAL BLOCKS, GUS, 2HOLE, 24-6 AWG		A
SIZE	PART NO.	
X	REB-A2E-XX	
REF:	S00067C	SHEET 1 OF 1