




APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Apr
-		RELEASED	10/7/22	
A		UPDATE SPEC.	9/8/23	LH/RC



ADAM-P/N	Color
REB-B2B-YG	YELLOW/GREEN




REB-B 2 B -XX

CSA (Cross Sectional Area)
Solid/Stranded
Solid: 24-12 Awg (0.2-4.0mm <sup>2</sup> )
Stranded: 24-14 Awg (0.2-2.5mm <sup>2</sup> )

Color
OR=Orange
BU=Blue
GY=Gray
YG=Yellow/Green

RECOMMENDED RAIL SIZE  
35.0mm X 7.5mm



ADAM-P/N	Color
REB-B2B-OR	ORANGE
REB-B2B-BU	BLUE
REB-B2B-GY	GRAY
REB-B2B-YG	YELLOW/GREEN

**SPECIFICATIONS:**

**Material:**  
 Insulator: PA66, rated UL 94V-0  
 Insulator Color: See Chart  
 Contacts: Copper Alloy, Tin Plated  
**Electrical:**  
 Voltage rating: 600 VAC  
 Current rating: 20 Amp  
 Dielectric withstanding voltage: 2200 VAC for 1 minute  
**Mechanical:**  
 Recommended Wire Size:  
 Solid: 24-12AWG (0.2-4.0mm<sup>2</sup>)  
 Stranded: 24-14AWG (0.2-2.5mm<sup>2</sup>)  
 Stripping Length: .315"~.394" (8-10mm)  
 Temperature Rating:  
 Operating temperature: -40°C to +105°C  
**Environmental:**  
 Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED		
INCHES		HOLES
.X	± .10	∅X ±.10
.XX	± .020	∅XX ±.015
.XXX	± .015	∅XXX ±.010



909 Rahway Avenue,  
 Union, NJ 07083  
 Phone: 908-687-5000  
 Fax: 908-687-5710

DRAWN	WX	10/7/22
CHECKED	RC	10/7/22
APPROVED		
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH		

TITLE		
DIN RAIL TERMINAL BLOCKS, GUV 2 HOLE, 24-12 AWG		
SIZE	PART NO.	REV.
X	REB-B2B-XX	A
REF:	S00067C	SHEET 1 OF 1

SCALE: NTS