





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/7/22	
A		UPDATE SPEC.	9/8/23	LH/RC



ADAM-P/N	Color
REB-B2E-YG	YELLOW/GREEN




SPECIFICATIONS:

Material:
 Insulator: PA66, rated UL 94V-0
 Insulator Color: See Chart
 Contacts: Copper Alloy, Tin Plated
 Electrical:
 Voltage rating: 600 VAC
 Current rating: 60 Amp
 Dielectric withstanding voltage: 2200 VAC for 1 minute
 Mechanical:
 Recommended Wire Size:
 Solid: 20-6AWG (0.5-16.0mm²)
 Stranded: 20-8AWG (0.5-10.0mm²)
 Stripping Length: .709" (18mm)
 Temperature Rating:
 Operating temperature: -40°C to +105°C
 Environmental:
 Lead free, RoHS compliant.



RECOMMENDED RAIL SIZE
35.0mm X 7.5mm



CSA (Cross Sectional Area)	Color
Solid/Stranded	OR=Orange
Solid: 20-6 Awg (0.5-16.0mm ²)	BU=Blue
Stranded: 20-8 Awg (0.5-10.0mm ²)	GY=Gray
	YG=Yellow/Green

ADAM-P/N	Color
REB-B2E-OR	ORANGE
REB-B2E-BU	BLUE
REB-B2E-GY	GRAY
REB-B2E-YG	YELLOW/GREEN

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED		
INCHES		HOLES
.x ± .10		∅x ± .10
.xx ± .020		∅xx ± .015
.xxx ± .015		∅xxx ± .010
DRAWN	WX	10/7/22
CHECKED	RC	10/7/22
APPROVED		
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH		



909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE		DIN RAIL TERMINAL BLOCKS, GUV 2 HOLE, 20-6 AWG	
SIZE	PART NO.	REV.	
X	REB-B2E-XX	A	
REF:	S00067C	SCALE:	NTS
		SHEET	1 OF 1