






APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	04/06/05	
A		REDRAWN	8/16/10	



CONTACT PIN	BRASS	TIN PLATED
CENTER CONTACT	P-BRONZE	GOLD PLATED
INSULATOR	POM	WHITE
INSULATOR	PP	NATURAL
INSULATOR	POM	WHITE
BODY	ZINC	NICKEL PLATED
DESCRIPTION	MATERIAL	FINISHED

SPECIFICATIONS:

Electrical:
Nominal Impedance: 50 ohms
Frequency range: 0-4 GHz
Contact Resistance: 3 Milliohms max. (Center Contact)
2 Milliohms max. (Outer Contact)
Insulator Resistance: 5000 Megohms min.
Environmental:
Lead free, RoHS compliant.

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

BNC FEMALE RIGHT ANGLE PCB MOUNT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				INCHES				HOLES			
.X	± .10	Ø.X	± .10	.XX	± .020	Ø.XX	± .015	.XXX	± .015	Ø.XXX	± .010
APPROVALS				DATE							
DRAWN	SS		04/06/05								
CHECKED											
APPROVED											
TITLE				BNC FEMALE RIGHT ANGLE PCB MOUNT							
SIZE				PART NO.							
X				RF1-29-D-00-50							
REF:				S00049T							
SCALE:				NTS							
SHEET				1 OF 1							

