


Rev	AWO #	Description	Date	Appr
-		RELEASED	10/18/11	

APPROVED: _____
DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:
Body: Zinc Alloy, Nickel plated
Contacts: Phosphor Bronze, Gold plated
Insulator: TPX

Electrical:
Nominal Impedance: 75 ohms
Frequency range: 0-1 GHz
Working Voltage: 500 VRMS max.
Dielectric Withstanding Voltage: 1500 VRMS min.
Contact Resistance: 3 Milliohms max. (Center Contact)
2 Milliohms max. (Outer Contact)
Insulator Resistance: 5000 Megohms min.
Environmental:
Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES			
.X	± .10	ØX	± .10
.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010
APPROVALS		DATE	
DRAWN	AY	10/18/11	
CHECKED	NP	10/18/11	
APPROVED			

ADAM TECH
909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

BNC CONNECTOR, 75Ω

SIZE	PART NO.	REV.
X	RF1-95-T-00-75	-
REF:	S00049T	SCALE: NTS
		SHEET 1 OF 1