




APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	08/01/09	
A		UPDATE DRAWING	4/21/21	LH/RC



4	COVER TAPE	PI	AMBER
3	CONTACT PIN	PB CU	GOLD
2	INSULATOR	PTFE	WHITE
1	BODY	BRASS	GOLD
NO.	DESCRIPTION	MATERIAL	FINISH

Electrical:
 Frequency range: DC-6 GHz
 Nominal Impedance: 50 OHM
 Voltage rating: 335 Volts max
 Temperature Rating:
 Operating temperature: -55°C to +155°C
 Environmental:
 Lead free, RoHS compliant.

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

DRAWN	SS	08/01/09
CHECKED		
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM
TECH

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE MCX JACK, PCB, VERTICAL		
SIZE X	PART NO. RF11-01-T-00-50-G	REV. -
REF: S00277T	SCALE: NTS	SHEET 1 OF 1