




APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-	9184	REDRAWN	10/21/08	
A	12318	REVISED DIM.	07/27/12	



CAP	BRASS	GOLD
FERRULE	BRASS	GOLD
DIELECTRIC	TEFLON	NONE
PIN	PHOS BRONZE	GOLD
BODY	BERYLLIUM	GOLD
BODY	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:
Nominal Impedance: 50 ohms
Frequency range: 0–6 GHz
Maximum working voltage: 335 VAC
Insulation resistance: 1000 Mohm min
Dielectric withstanding voltage: 1000 VAC rms min
Environmental:
Lead free, RoHS compliant.

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

TITLE

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

MCX MALE R/A CRIMP FOR RG174

APPROVALS	DATE	SIZE	PART NO.	REV.
DRAWN	DY	10/21/08		
CHECKED				
APPROVED				
REF:	S00011T	SCALE: NTS	SHEET 1 OF 1	