

6

5

4

3

2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/12/16	

D




C

B

D

C

B



RECOMMENDED PCB LAYOUT

COVER TAPE	PI	AMBER
CONTACT PIN	BERYLLIUM COPPER	GOLD
INSULATOR	PTFE	WHITE
BODY	BRASS	GOLD
ITEM NAME	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Nominal Impedance: 50 Ohms

Frequency range: DC-6 GHz

Working Voltage: 170 V max

Proof Voltage: 500 V

Temperature Rating:

Operating temperature: -55°C to +155°C

Environmental:

Lead free, RoHS compliant.

RoHS
COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 ØX ± .10
.XX ± .020 ØXX ± .015
.XXX ± .015 ØXXX ± .010

APPROVALS		DATE
DRAWN	HR	5/12/16
CHECKED	LW	5/12/16
APPROVED		
SIZE X		PART NO. RF12-41-T-00-50-G
REF: S00277T		REV. -
SCALE: NTS		SHEET 1 OF 1

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE
RF CONNECTOR, TYPE MMCX ST. JACK,
50 OHM, SURFACE MOUNT