



APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/10/06	
A		REDRAWN	5/15/12	



INSULATOR	TEFLON	NONE
PIN	Be Cu	GOLD
BODY	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:
Electrical:
Nominal Impedance: 50 ohms
Frequency range: 0-6 GHz
Working Voltage: 170 VRMS max.
Dielectric Withstanding Voltage: 500 VRMS min.
Contact Resistance: 5 Milliohms max. (Center Contact)
2.5 Milliohms max. (Outer Contact)
Insulator Resistance: 1000 Megohms min.
Environmental:
Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MM [INCHES]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010
APPROVALS DATE

DRAWN	SLS	1/10/06
CHECKED		
APPROVED		

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-0214
TITLE
RF CONNECTOR, TYPE MMCK,
VERTICAL, 50 OHM, PCB MOUNT

SIZE	PART NO.	REV.
X	RF12-05-T-00-50-G	A
REF:	S00011T	SCALE: NTS
SHEET 1 OF 1		