





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-	8719	RELEASED	5/7/08	
A		REDRAWN	5/9/16	AY/NP



FERRULE	BRASS	GOLD
CONTACT PIN	BRASS	GOLD
RING	BE CU	GOLD
BODY	BRASS	GOLD
INSULATOR	PTFE	WHITE
BARREL	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Frequency Range: DC-6 GHz

Normal Impedance: 50 ohm

Operating voltage: 170 Volts max.

Proof voltage: 500 Volts

VSWR: 1.3 max. @ 1 GHz

Temperature Rating:

Operating temperature: -55°C to +155°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MM [INCHES]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	SS	5/7/08
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-0214

TITLE
RF CONNECTOR, TYPE MMCX, MALE CRIMP
FOR RG174/U, 316/U, LMR-100, 50 OHM

SIZE X	PART NO. RF12-06-T-02-50-G	REV. A
REF: S00277T	SCALE: NTS	SHEET 1 OF 1