


Rev	AWO #	Description	Date	Appr
-	9468	RELEASED	4/10/09	

APPROVED: _____

DATE: _____ TITLE: _____



PIN	Be Cu	GOLD
INSULATOR	TEFLON	NONE
BODY	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:
 Nominal Impedance: 50 ohms
 Frequency range: 0–6 GHz
 Working Voltage: 170 VRMS max.
 Dielectric Withstanding Voltage: 500 VRMS min.
 Contact Resistance: 5 Milliohms max. (Center Contact)
 2.5 Milliohms max. (Outer Contact)
 Insulator Resistance: 1000 Megohms min.
 Environmental:
 Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

MMCX JACK FOR PCB

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				TITLE			
INCHES				HOLES			
.X ± .10				Ø.X ± .10			
.XX ± .020				Ø.XX ± .015			
.XXX ± .015				Ø.XXX ± .010			
APPROVALS				DATE			
DRAWN				DY			
4/10/09							
CHECKED							
APPROVED							
SIZE				PART NO.			
X				RF12-07-T-00-50-G			
REF:				S00011T			
SCALE:				NTS			
SHEET				1 OF 1			