

6

5

4

3

2

1

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/2/15	

APPROVED: _____


DATE: _____ TITLE: _____

D

D

C

C



B

B

CONTACT PIN	BE CU	GOLD
INSULATOR	PTFE	WHITE
BODY	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Nominal Impedance: 50 ohms

Frequency range: 0–6 GHz

Working Voltage: 170 VOLTS Max

Proof Voltage: 500 VOLTS

Temperature Rating:

Operating temperature: –55°C to +155°C

Environmental:

Lead free, RoHS compliant.



A

A

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

.X	± .10	ØX	± .10
.XX	± .020	ØXXX	± .015
.XXX	± .015	ØXXX	± .010

APPROVALS

DRAWN	AY	9/2/15
CHECKED	AC	9/2/15
APPROVED		

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

**RF CONNECTOR, TYPE MMCX ST. JACK,
50 OHM, PCB MOUNT**

TITLE	SIZE	PART NO.	REV.
	X	RF12-07B-T-00-50-G	-

REF: S00277 SCALE: NTS SHEET 1 OF 1

6

5

4

3

2

1