




APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/2/15	
A		ADDED TOLERANCE	10/29/15	
B		UPDATED INSULATOR SHAPE	11/3/15	HR/TW
C		UPDATE PLATE SPECIFICATION	12/11/15	HR/TW



RECOMMENDED PCB LAYOUT

PIN	BERYLLIUM COPPER	30u" GOLD
INSULATOR	TEFLON	
BODY	BRASS	GOLD FLASH
ITEM NAME	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Nominal Impedance: 50 ohms

Frequency range: 0–6 GHz

SWR: 1.25 max

Temperature Rating:

Operating temperature: –65°C to +165°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X $\pm .10$ $\phi .X$ $\pm .10$.XX $\pm .020$ $\phi .XX$ $\pm .015$.XXX $\pm .015$ $\phi .XXX$ $\pm .010$			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS			DATE		
DRAWN	HR		10/2/15	TITLE	
CHECKED	TW		10/2/15	RF CONNECTOR, TYPE MMCX ST. JACK, 50 OHM, PCB MOUNT	
APPROVED				SIZE	PART NO.
				X	RF12-07D-T-00-50-G
REF: S00049T			SCALE: NTS		REV. C
			SHEET 1 OF 1		