

6

5

4

3

2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev

AWO #

Description

Date

Appr

-

RELEASED




7/20/16

D

D

C

C



RECOMMENDED PCB LAYOUT

B

B

CONTACT PIN	BE CU	GOLD
INSULATOR	PTFE	WHITE
BODY	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:**Electrical:**

Nominal Impedance: 50 ohms

Frequency range: 0–6 GHz

Working Voltage: 170 VOLTS Max

Proof Voltage: 500 VOLTS

Temperature Rating:

Operating temperature: –55°C to +155°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS

DATE

DRAWN

AY

7/20/16

CHECKED

SY

7/20/16

APPROVED

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

RF CONNECTOR, TYPE MMCX ST. JACK,
50 OHM, PCB MOUNT

SIZE

X

PART NO.

RF12-07E-T-00-50-G

REV.

-

REF: S00277T

SCALE: NTS

SHEET 1 OF 1

6

5

4

3

2

1

A

A