





6 5 4 3 2 1

APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/2/15	



RECOMMENDED
CABLE STRIPPING DIM'S



FERRULE	BRASS	GOLD
COVER	BRASS	GOLD
INSULATOR	POM	NATURAL
CONTACT PIN	BRASS	GOLD
RING	BERYLLIUM COPPER	GOLD
BODY	BRASS	GOLD
INSULATOR	PTFE	WHITE
BARREL	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Frequency Range: DC–6 GHz

Normal Impedance: 50 ohm

Operating voltage: 170 VOLTS max.

Proof voltage: 500 VOLTS

VSWR: 1.3 max. @ 3 GHz

Temperature Rating:

Operating temperature: –55°C to +155°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS			TITLE		
DRAWN	HR	9/2/15	RF CONNECTOR, TYPE MMCX, RIGHT ANGLE, 50 OHM, 178U		
CHECKED	AC	9/2/15	SIZE	PART NO.	REV.
APPROVED			X	RF12-08A-T-21-50-G	-
REF: S00277T			SCALE: NTS		SHEET 1 OF 1