

6

5

4

3




2

1

Rev	AWO #	Description	Date	Appr
-		RELEASED	2/12/09	

APPROVED: _____

DATE: _____ TITLE: _____



NO	DESCRIPTION	MATERIAL	FINISH	QTY
9	GASKET	RUBBER	ORANGE	1
8	RETAINING RING	SK-5	NICKEL	1
7	SPRING	SK-5	NICKEL	1
6	WASHER	IRON	NICKEL	1
5	SHELL	BRASS	NICKEL	1
4	FERRULE	BRASS	NICKEL	1
3	DIELECTRIC	DELIN	NONE	1
2	PIN	BRASS	GOLD	1
1	BODY	BRASS	NICKEL	1

SPECIFICATIONS:

Electrical:

Impedance: 50 ohms

Frequency range: 0-4 GHz

Working Voltage: 500 VRMS max.

Dielectric Withstanding Voltage: 1500 VRMS min.

Contact Resistance: 3 Milliohms max. (Center Contact)

2 Milliohms max. (Outer Contact)

Insulator Resistance: 5000 Megohms min.

Environmental:

Lead free, RoHS compliant.

ADAM TECH

909 Ratway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

BNC MALE CRIMP FOR H155 LMR240

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES
HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS

DATE

DRAWN DY 2/12/09

CHECKED CH 2/12/09

APPROVED

SIZE PART NO.

RF1-03-D-20-50

REV.

-

REF: S00011T

SCALE: NTS

SHEET 1 OF 1

6

5

4

3

2

1