

6

5

4

3

2


1

Rev	AWO #	Description	Date	Appr
-	9362	RELEASED	2/16/09	


APPROVED: _____

DATE: _____ TITLE: _____

D




C



B

FERRULE	BRASS	NICKEL	1
FERRULE	BRASS	NICKEL	1
SLEEVE	ABC	NONE	1
CONTACT PIN	BRASS	GOLD	1
WASHER	IRON	NICKEL	1
SPRING	65Mn	NONE	1
OUT CONTACT	ZINC	NICKEL	1
GASKET	PVC	NONE	1
INSULATOR	TEFLON	NONE	1
BODY	BRASS	NICKEL	1
SHELL	ZINC	NICKEL	1
DESCRIPTION	MATERIAL	FINISH	QTY



SPECIFICATIONS:

Electrical:

Impedance: 75 ohms

Frequency range: 0–4 GHz

Working Voltage: 500 VRMS max.

Dielectric Withstanding Voltage: 1500 VRMS min.

Contact Resistance: 3 Milliohms max. (Center Contact)

2 Milliohms max. (Outer Contact)

Insulator Resistance: 5000 Megohms min.

Environmental:

Lead free, RoHS compliant.

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

BNC MALE CRIMP FOR RG179, 75 OHM

A

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE IN INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X $\pm .10$ Ø.X $\pm .10$
.XX $\pm .020$ Ø.XX $\pm .015$
.XXX $\pm .015$ Ø.XXX $\pm .010$

APPROVALS

DATE

DRAWN DY 2/16/09

CHECKED CH 2/16/09

APPROVED

SIZE PART NO.

RF1-03-T-03-75

REV.

-

REF: S00049T

SCALE: NTS

SHEET 1 OF 1

6

5

4

3

2

1