



APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/15/07	
A		UPDATE DRAWING	10/22/14	HR/VC



DESCRIPTION	MATERIAL	FINISH
BODY	BRASS	NICKEL
INSULATOR	TEFLON	
CENTER PIN	BRASS	GOLD

ELECTRICAL SPECIFICATIONS:

Impedance: 75 ohms.
Frequency Range: 0–1 GHz
Contact Resistance: 3 mohms max. (Center contact)
Insulation Resistance: 2 mohms max. (Outer contact)
VSWR: 1.3 max.
ENVIRONMENTAL:
Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908–687–5000 Fax: 908–687–5710

BNC CONNECTOR PCB MOUNT, 75 OHM

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED				INCHES				Holes			
.X	± .10	ØX	± .10	.XX	± .020	ØXX	± .015	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE							
DRAWN				BW				3/15/07			
CHECKED											
APPROVED											
SIZE				PART NO.				REV.			
X				RF1-07-1-00-75				A			
REF: S00049T				SCALE: NTS				SHEET 1 OF 1			