





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-	12196	RELEASED	05/18/12	
A	12196	REVISED SPEC.	02/22/13	



WASHER	STEEL	NICKEL
NUT	BRASS	NICKEL
GROUND RING	BRASS	NICKEL
CONTACT PIN	BRASS	GOLD
INSULATOR	DELRIIN	WHITE
BODY	BRASS	NICKEL
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:
Nominal Impedance: 50 ohms
Frequency range: 0-4 GHz
Maximum peak voltage: 500V
Insulation resistance: 5000 Mohm min @ 500 VDC
Dielectric withstanding voltage: 1500 VAC rms
Environmental:
Lead free, RoHS compliant.

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710
BNC FEMALE ISOLATED GROUND
BULKHEAD, 50 OHM

APPROVALS		DATE	TITLE	
DRAWN	TW	05/18/12	SIZE	PART NO.
CHECKED	NP	05/18/12	X	RF1-08-D-00-50-HDW
APPROVED			REF: S00049T	SCALE: NTS
			SHEET 1 OF 1	