




Rev	AWO #	Description	Date	Appr
-		RELEASED	7/4/12	

APPROVED: _____


DATE: _____ TITLE: _____




RECOMMENDED PCB LAYOUT



LOCK WASHER



CLAMP NUT



RECOMMENDED MOUNTING HOLE

NUT	BRASS	NICKEL
WASHER	STEEL	NICKEL
SOLDER TAIL	COPPER WIRE	TIN
MOUNTING POST	BRASS	TIN
INSULATOR	PE-606	NONE
BODY	ZINC ALLOY	NICKEL
CENTER CONTACT	PHOSPHOR BRONZE	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:
Nominal Impedance: 75 ohms
Frequency range: 0-1 GHz
Working Voltage: 500 VRMS max.
Dielectric Withstanding Voltage: 1500 VRMS min.
Contact Resistance: 3 Milliohms max. (Center Contact)
2 Milliohms max. (Outer Contact)
Insulator Resistance: 5000 Megohms min.
Environmental:
Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
BNC CONNECTOR, R/A, PCB, MOUNT JACK
METAL BODY WITH FITTING, 75 OHM

APPROVALS	DATE	SIZE	PART NO.	REV.
DRAWN	AY	7/4/12		
CHECKED	CC	7/4/12		
APPROVED				

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED	
INCHES	HOLES
.X ± .10	Ø.XX ± .10
.XX ± .020	Ø.XXX ± .015
.XXX ± .015	Ø.XXX ± .010
APPROVALS	
DRAWN	AY
CHECKED	CC
APPROVED	

REF:	S00049T	SCALE:	MKS	SHEET	1 OF 1
------	---------	--------	-----	-------	--------