



Rev	AWO #	Description	Date	Appr
-		RELEASED	4/9/14	

APPROVED: _____

DATE: _____ TITLE: _____



NUT	ZINC	NICKEL
WASHER TAIL	BRASS	NICKEL
WASHER	IRON	NICKEL
CENTER CONTACT	PHOSPHOR BRONZE	GOLD
INSULATOR	POM	NATURAL COLOR
BODY	ZINC	NICKEL
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Impedance: 50 ohm
Frequency range: 0-4 GHz
Working Voltage: 500 VRMS max.
Dielectric Withstanding Voltage: 1500 VRMS min.
V.S.W.R: 1.3 max
Contact Resistance: 3 Milliohms max. (Center Contact)
2 Milliohms max. (Outer Contact)
Insulator Resistance: 5000 Megohms min.
Environmental:
Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

BNC FEMALE BULKHEAD RECEPTACLE, 50 ohm

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES		
.X	± .10	ØX ± .10
.XX	± .020	ØXX ± .015
.XXX	± .015	ØXXX ± .010
APPROVALS		
DRAWN	HR	4/9/14
CHECKED	CH	4/9/14
APPROVED		

TITLE		
SIZE	PART NO.	REV.
X	RF1-106-D-00-50-HDW	-
REF: S00049T	SCALE: NTS	SHEET 1 OF 1