


Rev	AWO #	Description	Date	Appr
-		RELEASED	06/07/12	

APPROVED: _____

DATE: _____ TITLE: _____



WASHER	BRASS	NICKEL
DIELECTRIC	DELFIN	NONE
PIN	BRASS	GOLD
BODY	BRASS	NICKEL
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Nominal Impedance: 50 ohm

Frequency range: 0-4 GHz

Working Voltage: 500 VRMS Max.

VSWR: 1.3 max. (Straight)

1.5 max. (Right Angle)

Contact Resistance: 3 Milliohms max. (Center Contact)

2 Milliohms max. (Outer Contact)

Insulator Resistance: 5,000 Megohms min.

Environmental:

Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

BNC JACK ADAPTOR, 50 OHMS

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED				TITLE			
INCHES				Holes			
.X ± .10				ØX ± .10			
.XX ± .020				ØXX ± .015			
.XXX ± .015				ØXXX ± .010			
APPROVALS				DATE			
DRAWN		TW		06/07/12			
CHECKED		AY		06/07/12			
APPROVED							
SIZE		PART NO.		REV.			
X		RF1-99-D-AS-50		-			
REF:		S00049T		SCALE: NTS			
				SHEET 1 OF 1			