


APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/3/17	



GROUND CONTACT	COPPER ALLOY	GOLD
INNER CONTACT	COPPER ALLOY	GOLD
HOUSING	LCP UL94V-0	
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Frequency range: DC~6 GHz

Nominal Impedance: 50 Ohms

Rated Voltage: AC 60Vrms

VSWR: 1.3 max. @ 0.1~3 GHz
1.4 max. @ 3~6 GHz

Temperature Rating:

Operating temperature: -40°C to +80°C

Environmental:

Lead free, RoHS compliant.



PACKAGED ON TAPE & REEL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS			TITLE		
DATE			RF CONNECTOR, MICRO COAXIAL		
DRAWN			50 OHMS, VERTICAL, TAPE & REEL		
AY					
10/3/17					
CHECKED			SIZE		
MY			X		
10/3/17			PART NO.		
APPROVED			RF20-01B-L-00-50-G-T/R		
			REV.		
			-		
			REF: S00291T		
			SCALE: NTS		
			SHEET 1 OF 1		