




APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/20/16	



RECOMMENDED CABLE STRIPPING DIMS



FERRULE	BRASS	GOLD
CONTACT PIN	BRASS	GOLD
SHELL	BRASS	GOLD
GASKET	SILICONE	RED
RING	SUS 304	NATURAL
INSULATOR	PTFE	WHITE
BURREL	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:
Frequency range: DC-6 GHz
Nominal Impedance: 50 Ohms
Working Voltage: 250 VOLTS max
Proof Voltage: 750 VOLTS
VSWR : 1.3 Max @ 3 GHz
Temperature Rating:
Operating temperature: -65°C to +165°C
Environmental:
Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS			TITLE		
DRAWN	AY	7/20/16	RF CONNECTOR, SMA STR PLUG, 50OHM RG-174/U, 316/U, LMR-100		
CHECKED	SY	7/20/16	SIZE	PART NO.	REV.
APPROVED			X	RF2-02B-T-02-50-G	-
REF: S00277T			SCALE: NTS		SHEET 1 OF 1