



Rev	AWO #	Description	Date	Appr
-		RELEASED	3/6/13	

APPROVED: _____

DATE: _____ TITLE: _____



DIELECTRIC	TEFLON	NONE
PIN	BRASS	GOLD
BODY	BASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Frequency range: 0–18 GHz

Working Voltage: 250 VRMS max.

Dielectric Withstanding Voltage: 750 VRMS min.

Contact Resistance: 6 Milliohms max. (Center Contact)

2 Milliohms max. (Outer Contact)

Insulator Resistance: 5000 Megohms min.

Environmental:

Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

SMA JACK R/A PCB MOUNT, PLUG PIN

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.XX ± .10
.XX ± .020 Ø.XXX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS

DATE

DRAWN AY 3/6/13

CHECKED AH 3/6/13

APPROVED 3/6/13

SIZE PART NO.

X RF2-03-T-00-50-G-RP

REV.

-

REF: S00054T

SCALE: NTS

SHEET 1 OF 1