

6

5

4

3



2

1

Rev	AWO #	Description	Date	Appr
-		RELEASED	12/19/14	

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED P.C.B. LAYOUT

BODY	BRASS	GOLD
PIN	BRASS	GOLD
INSULATOR	TEFLON	NONE
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Nominal Impedance: 50 ohms

Frequency range: 0-6 GHz

SWR: 1.5 (Right Angle) max.

Environmental:

Lead free, RoHS Compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES [MM] TOLERANCES: EXCEPT AS NOTED	
INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010
APPROVALS	
DRAWN	AY
CHECKED	WY
APPROVED	

TITLE	
ADAM TECH	
909 Rahway Avenue, Union, NJ 07083	
Phone: 908-687-5000 Fax: 908-687-5710	
SMA JACK R/A PCB MOUNT, FEMALE PIN	

SIZE	PART NO.	REV.
X	RF2-03B-T-00-50-G	-
REF:	S00243T	SCALE: NTS
SHEET 1 OF 1		