




APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	12/15/17	
A		UPDATE DRAWING	10/23/18	AY/RC
B		UPDATE SPEC.	10/15/20	AY/TL



RECOMMENDED PCB LAYOUT

CONTACT PIN	BRASS	GOLD
INSULATOR	PTFE	WHITE
BODY	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Nominal Impedance: 50 ohms

Frequency range: DC-6 GHz

Working voltage: 500 VOLTS max.

Proof voltage: 1,000 VOLTS

VSWR: 1.2 max

Insert Loss: 0.3dB

Temperature Rating:

Operating temperature: -65°C to +165°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	AY	12/15/17
CHECKED	RC	12/15/17
APPROVED		

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE RF CONNECTOR, SMA STR PCB JACK			
SIZE X	PART NO. RF2-04A-T-00-50-G	REV. B	
REF: S00277T	SCALE: NTS	SHEET 1 OF 1	