



APPROVED: _____
DATE: _____ TITLE: _____







Rev	AWO #	Description	Date	Appr
-		RELEASED	7/20/16	



RECOMMENDED CABLE STRIPPING DIMS



RECOMMENDED MOUNTING HOLE



HEX NUT	BRASS	GOLD
WASHER	BRASS	GOLD
O-RING	SILICONE	RED
FERRULE	BRASS	GOLD
CONTACT PIN	BRASS	GOLD
INSULATOR	PTFE	WHITE
BURREL	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:
Frequency range: DC-6 GHz
Nominal Impedance: 50 Ohms
Working Voltage: 250 VOLTS max
Proof Voltage: 750 VOLTS
VSWR : 1.3 Max @ 1 GHz
Temperature Rating:
Operating temperature: -65°C to +165°C
Environmental:
Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	AY	7/20/16
CHECKED	SY	7/20/16
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
RF CONNECTOR, SMA JACK STR BULKHEAD
RG-174/U, 316/U, LMR-100

SIZE X	PART NO. RF2-06A-T-02-50-G	REV. -
REF: S00277T	SCALE: NTS	SHEET 1 OF 1