


APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/22/16	



FERRULE	COPPER	NICKEL
CONTACT PIN	BRASS	GOLD
INSULATOR	TEFLON	WHITE
BODY	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:
 Nominal Impedance: 50 ohms
 Frequency range: 0–6 GHz
 VSWR: 1.5 max.
 Working Voltage: 500 Vrms
 Insulator Resistance: 5,000 ohms min.
 Temperature Rating:
 Operating temperature: –55°C to +155°C
 Environmental:
 Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ±.10 Ø.X ±.10 .XX ±.020 Ø.XX ±.015 .XXX ±.015 Ø.XXX ±.010			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS DRAWN HR 4/22/16 CHECKED LW 4/22/16 APPROVED			TITLE SMA MALE CRIMP RIGHT ANGLE, RG316 RG174	
SIZE X			PART NO. RF2-153-T-02-50-G	REV. -
REF: S00128C			SCALE: NTS	SHEET 1 OF 1