






APPROVED: _____
DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	6/6/18	
A		ADDED P/N	12/20/18	AY/IW




RECOMMENDED P.C.B LAYOUT



RF55-33X-T-00-50-C-SH



RF55-33X-T-00-50-D-SH



Port Type

Type	Color	Item No
A	BLACK	RF55-33A-T-00-50-X-SH
B	WHITE	RF55-33B-T-00-50-X-SH
C	BLUE	RF55-33C-T-00-50-X-SH
D	BORDEAUX VIOLET	RF55-33D-T-00-50-X-SH
E	GREEN	RF55-33E-T-00-50-X-SH
F	BROWN	RF55-33F-T-00-50-X-SH
G	GREY	RF55-33G-T-00-50-X-SH
H	VIOLET	RF55-33H-T-00-50-X-SH
I	BEIGE	RF55-33I-T-00-50-X-SH
K	CURRY	RF55-33K-T-00-50-X-SH
Z	WATER BLUE	RF55-33Z-T-00-50-X-SH
L	CARMINE RED	RF55-33L-T-00-50-X-SH
M	PASTEL ORANGE	RF55-33M-T-00-50-X-SH
N	PASTEL GREEN	RF55-33N-T-00-50-X-SH

PLASTIC SHELL	PA66+30%GF	
INSULATOR	LCP	
INSULATOR	PTFE	
PIN CONTACT	PHOSPHOR BRONZE	GOLD
COVER	BRASS	NICKEL
BODY (FRONT)	BRASS	NICKEL
BODY (BACK)	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Frequency range: DC~4 GHz
Nominal Impedance: 50 ohms
Withstanding voltage: 335 V
Insulator Resistance: 1000 MΩ
Contact Resistance: 6 Milliohms max. (Center Contact)
1 Milliohms max. (Outer Contact)

Temperature Rating:
Operating temperature: -40°C to +85°C
Environmental:
Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± 0.25
.XX ± 0.15
.XXX ± 0.05

Ø.XX ± 0.13

APPROVALS		DATE
DRAWN	AY	6/6/18
CHECKED	MY	6/6/18
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

FAKRA PLUG SMB TYPE RIGHT ANGLE, FOR PCB

SIZE	PART NO.	REV.
X	RF55-33X-T-00-50-X-SH	A
REF:	S00134C	SCALE: NTS
SHEET 1 OF 1		