


Rev	AWO #	Description	Date	Appr
-		RELEASED	03/09/12	

APPROVED: _____

DATE: _____ TITLE: _____



ITEM	DESCRIPTION	MATERIAL	FINISH	QTY
1	BODY	BRASS	NICKEL	1
2	PIN	BRASS	GOLD	1
3	INSULATOR	DELRI	WHITE	1
4	GASKET	RUBBER	BLACK	1
5	WASHER	BRASS	NICKEL	1

SPECIFICATIONS:

Electrical:
Voltage Rating: 150V AC
Nominal Impedance: 50 ohms
Frequency range: 0-4 GHz
Maximum peak voltage: 500V
Insulation resistance: 500 Mohm min @ 500 VDC
Dielectric withstanding voltage: 500 VAC rms
VSWR: 1.2 max. 0-1,500 MHz
Environmental:
Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE

N FEMALE PANEL RECEPTACLE

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X .XX ± .020 Ø.XX .XXX ± .015 Ø.XXX .XXX ± .010 Ø.XXX				APPROVALS DRAWN TW 03/09/12 CHECKED AY 03/09/12 APPROVED		SIZE PART NO. X RF5-02-D-01-50		REV. -	
REF: S00049T SCALE: NTS SHEET 1 OF 1									