




Rev	AWO #	Description	Date	Appr
-		RELEASED	10/5/06	

APPROVED: _____
DATE: _____ TITLE: _____



NO	Description	Qty	Material	Finish
5	SHELL	1	BRASS	NICKEL
4	FERRULE	1	BRASS	NICKEL
3	DIELECTRIC	1	DELTRIN	NONE
2	PIN	1	BRASS	GOLD
1	BODY	1	BRASS	NICKEL

SPECIFICATIONS

Electrical

Nominal Impedance: 50 Ohms
Frequency Range: 0 – 4 GHz
Maximum Peak Voltage: 500V
Insulation Resistance: 5000 Mohms min @ 500 VDC
Dielectric Withstanding Voltage: 1500 VAC rms.
Environmental:
Lead free, RoHS compliant.
Recommended soldering temp: 235 for 5 sec.



ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

MINIATURE UHF, MALE CRIMP,
50 OHM, FOR RG58

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED				TITLE			
Holes .X ± .10 .XX ± .020 .XXX ± .015				DATE			
APPROVALS				REV.			
DRAWN SS				PART NO.			
CHECKED				RF9-01-D-01-50			
APPROVED				SCALE: NTS			
3				SHEET 1 OF 1			